

# MultipacPRO Mounting Plate



Mounting plates are designed for the mounting of heavy components, e.g. transformers.

## CERTIFICATIONS



## FEATURES

Mounting plates are designed for the mounting of heavy components, e.g. transformers

Bolted laterally inside on a 19" chassis

## SPECIFICATIONS

- Material:** Aluminum
- Works With:** Chassis
- Product Type:** Mounting Plate
- Product Family:** MultipacPRO

Table 1/1

| Catalog Number | Depth | Package Quantity | Rack Width | Width   | Certifications |
|----------------|-------|------------------|------------|---------|----------------|
| 20860-107      | 150mm | 1                | 84HP       | 402.5mm | RoHS           |
| 20860-112      | 450mm | 1                | 84HP       | 402.5mm |                |
| 20860-111      | 390mm | 1                | 84HP       | 402.5mm | RoHS           |
| 20860-108      | 210mm | 1                | 84HP       | 402.5mm | RoHS           |
| 20860-110      | 330mm | 1                | 84HP       | 402.5mm | RoHS           |
| 20860-109      | 270mm | 1                | 84HP       | 402.5mm | RoHS           |

## ADDITIONAL PRODUCT DETAILS

---

Mounting plates can also be fitted at the same time as the internal mounting for euroboards.

Where a mounting plate is used the clear mounting height is reduced by at least 2.5 mm.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**