

19" Front Panel

Data Solutions

Front panels made of Aluminum.



CERTIFICATIONS



FEATURES

Aluminum, 4 or 3 mm thick, with Anodized or Painted finish

SPECIFICATIONS

- Rack Width:** 95HP
- Material:** Aluminum
- Accessory Type:** Front panel
- Product Type:** Front Panel

Table 1/3

| Catalog Number | Rack Height | Depth (D) | Mounting | Finish | Front Finish | Package Quantity |
|----------------|-------------|-----------|----------------|---------------|--------------|------------------|
| 30118-299 | 1U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 30118-948 | 1U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 30219-098 | 1U | 3mm | Screw-on Front | Anodized | Anodized | 1 |

| CatalogNumber | Rack Height | Depth (D) | Mounting | Finish | Front Finish | Package Quantity |
|---------------|-------------|-----------|----------------|---------------|--------------|------------------|
| 40304-074 | 1U | 4mm | Screw-on Front | Anodized | Anodized | 1 |
| 30219-137 | 7U | 3mm | Screw-on Front | Anodized | Anodized | 1 |
| 30118-956 | 9U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 30219-113 | 6U | 3mm | Screw-on Front | Anodized | Anodized | 1 |
| 30219-110 | 5U | 3mm | Screw-on Front | Powder Coated | Anodized | 1 |
| 30219-107 | 4U | 3mm | Screw-on Front | Anodized | Anodized | 1 |
| 30118-949 | 2U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 30118-950 | 3U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 30219-104 | 3U | 3mm | Screw-on Front | Anodized | Anodized | 1 |
| 30118-951 | 4U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 30118-303 | 4U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 30219-101 | 2U | 3mm | Screw-on Front | Anodized | Anodized | 1 |
| 30118-952 | 5U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 30118-302 | 3U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 30118-953 | 6U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 30118-954 | 7U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 30118-957 | 10U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 30118-955 | 8U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 30118-301 | 2U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 40304-083 | 10U | 4mm | Screw-on Front | Anodized | Anodized | 1 |
| 40304-082 | 9U | 4mm | Screw-on Front | Anodized | Anodized | 1 |
| 40304-081 | 8U | 4mm | Screw-on Front | Anodized | Anodized | 1 |
| 40304-080 | 7U | 4mm | Screw-on Front | Anodized | Anodized | 1 |
| 40304-079 | 6U | 4mm | Screw-on Front | Anodized | Anodized | 1 |
| 40304-078 | 5U | 4mm | Screw-on Front | Anodized | Anodized | 1 |
| 40304-077 | 4U | 4mm | Screw-on Front | Anodized | Anodized | 1 |
| 40304-076 | 3U | 4mm | Screw-on Front | Anodized | Anodized | 1 |
| 30118-305 | 6U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 40304-075 | 2U | 4mm | Screw-on Front | Anodized | Anodized | 1 |
| 30118-306 | 7U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 30118-307 | 8U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 30219-144 | 10U | 3mm | Screw-on Front | Anodized | Anodized | 1 |
| 30118-304 | 5U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 30219-143 | 9U | 3mm | Screw-on Front | Anodized | Anodized | 1 |

| CatalogNumber | Rack Height | Depth (D) | Mounting | Finish | Front Finish | Package Quantity |
|---------------|-------------|-----------|----------------|---------------|--------------|------------------|
| 30118-308 | 9U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |
| 30219-138 | 8U | 3mm | Screw-on Front | Anodized | Anodized | 1 |
| 30118-309 | 10U | 3mm | Screw-on Front | Powder Coated | Painted | 1 |

Table 2/3

| Catalog Number | Rear Finish | Treated Edges | Color Code | EMC Shielding | Height (H) | Type |
|----------------|-------------|---------------|------------|---------------|------------|-----------------|
| 30118-299 | Painted | | RAL 7035 | No | 43.6mm | 19" Front Panel |
| 30118-948 | Painted | | RAL 7021 | No | 43.6mm | 19" Front Panel |
| 30219-098 | Anodized | No | | No | 43.6mm | 19" Front Panel |
| 40304-074 | Anodized | Yes | | No | 43.6mm | 19" Front Panel |
| 30219-137 | Anodized | No | | No | 310.3mm | 19" Front Panel |
| 30118-956 | Painted | | RAL 7021 | No | 399.2mm | 19" Front Panel |
| 30219-113 | Anodized | No | | No | 265.9mm | 19" Front Panel |
| 30219-110 | Anodized | No | | No | 221.4mm | 19" Front Panel |
| 30219-107 | Anodized | No | | No | 177mm | 19" Front Panel |
| 30118-949 | Painted | | RAL 7021 | No | 88.1mm | 19" Front Panel |
| 30118-950 | Painted | | RAL 7021 | No | 132.5mm | 19" Front Panel |
| 30219-104 | Anodized | No | | No | 132.5mm | 19" Front Panel |
| 30118-951 | Painted | | RAL 7021 | No | 177mm | 19" Front Panel |
| 30118-303 | Painted | | RAL 7035 | No | 177mm | 19" Front Panel |
| 30219-101 | Anodized | No | | No | 88.1mm | 19" Front Panel |
| 30118-952 | Painted | | RAL 7021 | No | 221.4mm | 19" Front Panel |
| 30118-302 | Painted | | RAL 7035 | No | 132.5mm | 19" Front Panel |
| 30118-953 | Painted | | RAL 7021 | No | 265.9mm | 19" Front Panel |
| 30118-954 | Painted | | RAL 7021 | No | 310.3mm | 19" Front Panel |
| 30118-957 | Painted | | RAL 7021 | No | 443.7mm | 19" Front Panel |
| 30118-955 | Painted | | RAL 7021 | No | 354.8mm | 19" Front Panel |
| 30118-301 | Painted | | RAL 7035 | No | 88.1mm | 19" Front Panel |
| 40304-083 | Anodized | Yes | | No | 443.7mm | 19" Front Panel |
| 40304-082 | Anodized | Yes | | No | 399.2mm | 19" Front Panel |
| 40304-081 | Anodized | Yes | | No | 354.8mm | 19" Front Panel |
| 40304-080 | Anodized | Yes | | No | 310.3mm | 19" Front Panel |
| 40304-079 | Anodized | Yes | | No | 265.9mm | 19" Front Panel |
| 40304-078 | Anodized | Yes | | No | 221.4mm | 19" Front Panel |

| CatalogNumber | Rear Finish | Treated Edges | Color Code | EMC Shielding | Height (H) | Type |
|---------------|-------------|---------------|------------|---------------|------------|-----------------|
| 40304-077 | Anodized | Yes | | No | 177mm | 19" Front Panel |
| 40304-076 | Anodized | Yes | | No | 132.5mm | 19" Front Panel |
| 30118-305 | Painted | | RAL 7035 | No | 265.9mm | 19" Front Panel |
| 40304-075 | Anodized | Yes | | No | 88.1mm | 19" Front Panel |
| 30118-306 | Painted | | RAL 7035 | No | 310.3mm | 19" Front Panel |
| 30118-307 | Painted | | RAL 7035 | No | 354.8mm | 19" Front Panel |
| 30219-144 | Anodized | No | | No | 443.7mm | 19" Front Panel |
| 30118-304 | Painted | | RAL 7035 | No | 221.4mm | 19" Front Panel |
| 30219-143 | Anodized | No | | No | 399.2mm | 19" Front Panel |
| 30118-308 | Painted | | RAL 7035 | No | 399.2mm | 19" Front Panel |
| 30219-138 | Anodized | No | | No | 354.8mm | 19" Front Panel |
| 30118-309 | Painted | | RAL 7035 | No | 443.7mm | 19" Front Panel |

Table 3/3

| Catalog Number | Width (W) |
|----------------|-----------|
| 30118-299 | 483mm |
| 30118-948 | 483mm |
| 30219-098 | 483mm |
| 40304-074 | 483mm |
| 30219-137 | 483mm |
| 30118-956 | 483mm |
| 30219-113 | 483mm |
| 30219-110 | 483mm |
| 30219-107 | 483mm |
| 30118-949 | 483mm |
| 30118-950 | 483mm |
| 30219-104 | 483mm |
| 30118-951 | 483mm |
| 30118-303 | 483mm |
| 30219-101 | 483mm |
| 30118-952 | 483mm |
| 30118-302 | 483mm |
| 30118-953 | 483mm |
| 30118-954 | 483mm |
| 30118-957 | 483mm |

| Catalog Number | Width (W) |
|----------------|-----------|
| 30118-955 | 483mm |
| 30118-301 | 483mm |
| 40304-083 | 483mm |
| 40304-082 | 483mm |
| 40304-081 | 483mm |
| 40304-080 | 483mm |
| 40304-079 | 483mm |
| 40304-078 | 483mm |
| 40304-077 | 483mm |
| 40304-076 | 483mm |
| 30118-305 | 483mm |
| 40304-075 | 483mm |
| 30118-306 | 483mm |
| 30118-307 | 483mm |
| 30219-144 | 483mm |
| 30118-304 | 483mm |
| 30219-143 | 483mm |
| 30118-308 | 483mm |
| 30219-138 | 483mm |
| 30118-309 | 483mm |

ADDITIONAL PRODUCT DETAILS

Please order 19" assembly kit separately.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE