

Barrette MSPO 0U 30 A (24 A) NA/32 A Int 380-415 V 3P Wye 6 CB combinaison de fermeture 36

Data Solutions

RÉFÉRENCE CATALOGUE

EN6883



The Advantage Series Outlet Metered, Outlet Switched PDU family offers energy metering with advanced power and environmental monitoring options and remote outlet on/off switching. Comprehensive monitoring at the input phase, circuit breaker, and individual outlet levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

FONCTIONS

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

UL 2900-1 certified for safety software cybersecurity for network-connectable products.

Dual network connectivity ports: 1x Gigabit Ethernet (10/100/1000 Mbps) and 1x (10/100 Mbps) connection/IP address

Ethernet cascading up to 64 PDUs

Each PDU can provide DC power sufficient to power network management electronics

Dual Ethernet ports for redundant network communications

Remote connectivity through HTTP(s), IPv4 and IPv6, SSH, Virtual Serial, SNMP (v1, v2c, v3), JSON-RPC, LDAP(S)

Data efficient REACT framework with native mobile device support

Tool-less hot swappable Network Management Card (NMC) with Cortex A-5 for microprocessing and memory that can be installed both upright and upside down for top or bottom power inputs

The border color of the NMC display is user programmable for power source identification by PDU

The NMC supports up to 10 digital sensors for environmental and/or electronic lock monitoring

Display languages include English, Spanish, German, French, Italian, Korean, Japanese, and Chinese (simplified)

ATTRIBUTS DU PRODUIT

Famille de produits: Enlogic

Type: PDU intelligent

Type de produit: Bâti de prises

Type de prise: (18) Verrouillage C13/C15; (18) Verrouillage C13/C15/C19/C21

Nombre de prises: 36

Couleur: Noir

Sorties commutées: Oui

Puissance nominale: 17,3 kVA Amérique du Nord; 22,1 kVA International

Longueur de câble: 3000mm

Disjoncteur: 20 A, 1 pôle, Hy-MagA

Nombre de disjoncteurs: 6

Tension nominale: 415V

Puissance de sortie nominale: 230VAC

Nombre de tensions de sortie: 36

Intensité (ampérage détaré): 30 A (24 A) Amérique du Nord; 32 A International

Unités de rack: 0U

Interrupteur marche/arrêt inclus: Oui

Tension de sortie: 208 – 230VAC

Type de mesure: Sortie

Type de prise: Double homologation CEI60309 530/532P6 (IP44)

Câble d'entrée amovible: Non

Matériau: Acier

Finition: Revêtement poudré

Hauteur: 1720mm

Largeur: 56mm

Profondeur: 75mm

Quantité par colis: 1

Longueur du câble d'entrée: 3m

INFORMATIONS PRODUIT COMPLÉMENTAIRES

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout

autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.



Notre gamme complète de marques:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE