

## Giunto a flangia 180-Max Syspend



Syspend 180-Max Flange Coupling attaches a tube to the enclosure, enabling 300-degree enclosure rotation and can be locked into a given position. The flange coupling has a safety stop and maintenance-free bearings.

### CARATTERISTICHE

---

Coupling can rotate 300 degrees with stop

Gasket, set screws, and mounting hardware are included

Assembled Syspend 180 HMI Arm System has a max weight load of 180 lb. (81.6 kg)

## SPECIFICHE

---

**Materiale:** Alluminio

**Finitura:** Verniciato a polvere

Table 1/1

Codice a catalogo	Altezza	Larghezza	Profondità	Colore	Codice colore
S1MFCG	101mm	125mm	100mm	Grigio chiaro	RAL 7035
S1MFC	174mm	133mm	125mm	Jet Black	RAL 9005

## AVVERTIMENTO

---

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Il nostro straordinario portafoglio di marchi:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**