


# Two Pole Distribution Block, 40 A, 2 Line Side & 15 Load Side Connections

## Data Solutions

### NÚMERO DE CATÁLOGO

**BD-40A**



### CERTIFICATIONS



### CARACTERISTICAS

Minimum space for maximum power

Protection cover and insulating screens are transparent

Insulating screen between each row

Easy and safe connections

Easily clips onto DIN rail or mounts to panel with screws

RoHS compliant

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

Halogen free

## CARACTERÍSTICAS DO PRODUTO

Número do artigo: 563720

Max Current Rating, IEC: 40A

Short Term Withstand Current (Icw) 1s: 4.5kA

Peak Short Circuit Current (Ipk): 22kA

Max Working Voltage, IEC (Ui): 500

Line Side Number of Connections: 2

Line Side Compact Stranded Wire Size: 6 - 16 mm<sup>2</sup>

Line Side Stranded Wire Size - Ferrule: 4 – 10mm<sup>2</sup>

Load Side Number of Connections: 15

Load Side Compact Stranded Wire Size: (15) 1,5 - 4 mm<sup>2</sup>

Load Side Stranded Wire Size - Ferrule: (15) 0,75 – 4 mm<sup>2</sup>

Profundidade (D): 50mm

Altura (H): 50mm

Largura (W): 130mm

Peso unitário: 0.22kg


Flammability Rating: UL® 94V-0

Em conformidade com: IEC® 60947-7-1

## DETALHES ADICIONAIS DO PRODUTO

Line side and load side number of connections are per pole.

## DIAGRAMAS



## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portfólio de marcas:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**