

19" Cable Ducting

19" unit for easy and effective cable management (cable ducting).



CERTIFICATIONS



CARACTERISTICAS

19" Front panel for cable ducting

ESPECIFICAÇÕES

Accessory Type: Front panel
Product Type: Front Panel
Material: Aço

Table 1/3

Número de catálogo	Rack Height	Instalação	Quantidade por embalagem	Front Finish	Rear Finish	Código de cor
20118-734	1U	Screw-on Front	1	Painted	Painted	RAL 7035
20118-767	1U	Screw-on Front	1	Painted	Painted	RAL 7021
20118-736	2U	Screw-on Front	1	Painted	Painted	RAL 7035
20118-768	2U	Screw-on Front	1	Anodized	Conductive	RAL 7021

Table 2/3

Número de catálogo	Profundidade	EMC Shielding	Acabamento	Altura	Rack Width	Tipo
20118-734	1.5mm	Não	Pintura electrostática com Acabamento Texturado	43.6mm	95HP	19" Front Panel
20118-767	1.5mm	Não	Pintura electrostática com Acabamento Texturado	43.6mm	95HP	19" Front Panel
20118-736	1.5mm	Não	Pintura electrostática com Acabamento Texturado	88.1mm	95HP	19" Front Panel
20118-768	1.5mm	Não	Pintura electrostática com Acabamento Texturado	88.1mm	95HP	19" Front Panel

Table 3/3

Número de catálogo	Largura
20118-734	483mm
20118-767	483mm
20118-736	483mm
20118-768	483mm

DETALHES ADICIONAIS DO PRODUTO

Please order 19" assembly kit separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE