

19" Drawer



19" Drawers allow mounting of laptops, writing surfaces for easy operations. The SCHROFF 19" drawer has a load capacity of 15 KG, allowing a wide range of products to be assembled into the drawer.

CERTIFICATIONS



CARACTERISTICAS

Static load-carrying capacity 15 kg

Optional writing surface

ESPECIFICAÇÕES

- Static Load:** 15kg
- Product Type:** Cabinet/Rack Drawer
- Material:** Aço

Table 1/2

Número de catálogo	Rack Height	Acabamento	Quantidade por embalagem	Cor	Código de cor	Front Finish
20110-054	1U	Pintura electrostática com Acabamento Texturado	1	Light Grey	RAL 7035	

Número de catálogo	Rack Height	Acabamento	Quantidade por embalagem	Cor	Código de cor	Front Finish
20110-061	1U	Pintura electrostática com Acabamento Texturado	1			Anodized
20110-180	1U	Pintura electrostática com Acabamento Texturado	1	Black Grey	RAL 7021	
20110-056	3U	Pintura electrostática com Acabamento Texturado	1	Light Grey	RAL 7035	
20110-062	2U	Pintura electrostática com Acabamento Texturado	1			Anodized
20110-181	2U	Pintura electrostática com Acabamento Texturado	1	Black Grey	RAL 7021	
20110-063	3U	Pintura electrostática com Acabamento Texturado	1			Anodized
20110-055	2U	Pintura electrostática com Acabamento Texturado	1	Light Grey	RAL 7035	
20110-182	3U	Pintura electrostática com Acabamento Texturado	1	Black Grey	RAL 7021	

Table 2/2

Número de catálogo	Tipo	Works With
20110-054	Drawer	19" Cabinets
20110-061	Drawer	19" Cabinets

Número de catálogo	Tipo	Works With
20110-180	Drawer	19" Cabinets
20110-056	Drawer	19" Cabinets
20110-062	Drawer	19" Cabinets
20110-181	Drawer	19" Cabinets
20110-063	Drawer	19" Cabinets
20110-055	Drawer	19" Cabinets
20110-182	Drawer	19" Cabinets

DETALHES ADICIONAIS DO PRODUTO

Please order 19" assembly kit separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE