

CompacPRO Front Panel

The front panel for the CompacPRO Cases is bolted to the front frame of the case.



CERTIFICATIONS



CARACTERISTICAS

The front panel is bolted to the front frame of the enclosure

ESPECIFICAÇÕES

Material:	Aluminio
Acabamento:	Anodized
Accessory Type:	Front panel
Product Type:	Front Panel

Table 1/2

Número de catálogo	Rack Height	Rack Width	Profundidade	Quantidade por embalagem	Front Finish	Rear Finish
30823-227	4U	63HP	3mm	1	Anodized	Anodized
30823-209	2U	42HP	3mm	1	Anodized	Anodized
30823-224	3U	63HP	3mm	1	Anodized	Anodized
30823-284	6U	84HP	3mm	1	Anodized	Anodized
30823-254	3U	28HP	3mm	1	Anodized	Anodized
30823-272	4U	84HP	3mm	1	Anodized	Anodized

Número de catálogo	Rack Height	Rack Width	Profundidade	Quantidade por embalagem	Front Finish	Rear Finish
30823-269	4U	42HP	3mm	1	Anodized	Anodized
30823-257	3U	42HP	3mm	1	Anodized	Anodized
30823-260	3U	84HP	3mm	1	Anodized	Anodized
30823-215	2U	84HP	3mm	1	Anodized	Anodized
30823-230	6U	63HP	3mm	1	Anodized	Anodized

Table 2/2				
Número de catálogo	Treated Edges	EMC Shielding	Altura	Largura
30823-227	Não	Não	172.9mm	345.4mm
30823-209	Não	Não	84mm	238.7mm
30823-224	Não	Não	128.4mm	345.4mm
30823-284	Não	Não	261.8mm	452.1mm
30823-254	Não	Não	128.4mm	167.5mm
30823-272	Não	Não	172.9mm	452.1mm
30823-269	Não	Não	1729mm	238.7mm
30823-257	Não	Não	128.4mm	238.7mm
30823-260	Não	Não	128.4mm	452.1mm
30823-215	Não	Não	84mm	452.1mm
30823-230	Não	Não	261.8mm	345.4mm

DETALHES ADICIONAIS DO PRODUTO

Assembly Kit to fix one rear and one front panel is included with the case.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE