

# Interscale Desktop Case, Perforated



Flexible desktop case with integrated EMC protection and perforated sides. Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.

## CERTIFICATIONS



## CARACTERÍSTICAS

Modular desktop case consisting of 4 assembled parts

Developed according to IEC 60297-3-109 (under progress at IEC)

Integrated EMC protection

Ingress protection up to IP 20

Color RAL 7016

Modified or customized cases upon request

## ESPECIFICAÇÕES

<b>Material:</b>	Aluminio; Aço
<b>Tipo:</b>	Desktop
<b>Família de produtos:</b>	Interscale
<b>Grau de proteção:</b>	IP20
<b>Código de cor:</b>	RAL 7016
<b>Product Type:</b>	Small Form Factor Case

Table 1/2

Número de catálogo	Altura	Quantidade por embalagem	Largura	Profundidade	Cooling	Cor
14825-154	43.7mm	1	221mm	177mm	Perforated	Anthracite Grey
14825-254	88.1mm	1	221mm	177mm	Perforated	Anthracite Grey
14825-255	88.1mm	1	221mm	221mm	Perforated	Anthracite Grey
14825-197	43.7mm	1	399mm	310mm	Perforated	Anthracite Grey
14825-275	88.1mm	1	310mm	221mm	Perforated	Anthracite Grey
14825-195	43.7mm	1	399mm	221mm	Perforated	Anthracite Grey
14825-295	88.1mm	1	399mm	221mm	Perforated	Anthracite Grey
14825-297	88.1mm	1	399mm	310mm	Perforated	Anthracite Grey
14825-175	43.7mm	1	310mm	221mm	Perforated	Anthracite Grey
14825-375	132.6mm	1	310mm	221mm	Perforated	Anthracite Grey
14825-395	132.6mm	1	399mm	221mm	Perforated	Anthracite Grey
14825-155	43.7mm	1	221mm	221mm	Perforated	Anthracite Grey
14825-397	132.6mm	1	399mm	310mm	Perforated	Anthracite Grey

Table 2/2

Número de catálogo	Acabamento
14825-154	Aluminum-Zinc Plated, Pintura electrostática com Acabamento Texturado
14825-254	Aluminum-Zinc Plated, Pintura electrostática com Acabamento Texturado
14825-255	Aluminum-Zinc Plated, Pintura electrostática com Acabamento Texturado
14825-197	Aluminum-Zinc Plated, Pintura electrostática com Acabamento Texturado
14825-275	Aluminum-Zinc Plated, Pintura electrostática com Acabamento Texturado
14825-195	Aluminum-Zinc Plated, Pintura electrostática com Acabamento Texturado
14825-295	Aluminum-Zinc Plated, Pintura electrostática com Acabamento Texturado
14825-297	Aluminum-Zinc Plated, Pintura electrostática com Acabamento Texturado
14825-175	Aluminum-Zinc Plated, Pintura electrostática com Acabamento Texturado
14825-375	Aluminum-Zinc Plated, Pintura electrostática com Acabamento Texturado
14825-395	Aluminum-Zinc Plated, Pintura electrostática com Acabamento Texturado

Número de catálogo	Acabamento
14825-155	Aluminum-Zinc Plated, Pintura eletrostática com Acabamento Texturado
14825-397	Aluminum-Zinc Plated, Pintura eletrostática com Acabamento Texturado

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



O nosso forte portfólio de marcas:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**