


MultipacPRO 19" Chassis Basic Kit

Such a kit enables a customer to configure the 3 different top / bottom covers.



CERTIFICATIONS



CARACTERISTICAS

For non-standardized assemblies (1 ... 5 U) and standardized assemblies (1, 2 U) conforming to IEC 60297-3-105

Frame consists of two lateral parts and front/rear panel

Material: aluminium

Select further components (Accessories)

ESPECIFICAÇÕES

Material:	Aluminio
Tipo:	Configurable
Família de produtos:	MultipacPRO
EMC Shielding:	No (Retrofittable)
Product Type:	Subrack/Chassis

Table 1/1

Número de catálogo	Rack Height	Profundidade	Usable Width	Instalação	Em conformidade com
20860-201	1U	220mm	403mm	Rack	IEC 60297-3-100
20860-203	1U	340mm	403mm	Rack	IEC 60297-3-100

Número de catálogo	Rack Height	Profundidade	Usable Width	Instalação	Em conformidade com
20860-202	1U	280mm	403mm	Rack	IEC 60297-3-100
20860-212	2U	340mm	403mm	Rack	IEC 60297-3-100
20860-211	2U	280mm	403mm	Rack	IEC 60297-3-100
20860-210	2U	220mm	403mm	Rack	IEC 60297-3-100
20860-220	3U	340mm	403mm	Rack	IEC 60297-3-100
20860-219	3U	280mm	403mm	Rack	IEC 60297-3-100
20860-221	3U	400mm	403mm	Rack	IEC 60297-3-100
20860-222	3U	460mm	403mm	Rack	IEC 60297-3-100
20860-231	4U	460mm	403mm	Rack	IEC 60297-3-100
20860-230	4U	400mm	403mm	Rack	IEC 60297-3-100
20860-229	4U	340mm	403mm	Rack	IEC 60297-3-100
20860-228	4U	280mm	403mm	Rack	IEC 60297-3-100
20860-240	5U	460mm	403mm	Rack	IEC 60297-3-100

DETALHES ADICIONAIS DO PRODUTO

Please order mounting plate, cover and base plates, handles, telescopic slides separately.

Dimensions h = clear mounting height = H-8.1 mm, b = clear mounting width = 403 mm.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE