


Novastar Base/Plinth



Base Plate for Rear Cable Ducting which cut out for cable management. Opening is covered with plastic. Accessory brush strip can build in.

CERTIFICATIONS



CARACTERISTICAS

Static load-carrying capacity 400 kg

Adjustable feet, height 57 mm ... 67 mm

St, 1.5 mm, RAL 7021

Cable ducting 110 x 76 mm

Incl. GND/earthing

ESPECIFICAÇÕES

Altura: 45mm
Product Type: Cabinet/Rack Base
Material: Aço

Table 1/2

Número de catálogo	Largura	Profundidade	Quantidade por embalagem	Cor	Código de cor	Acabamento
27230-072	553mm	800mm	1	Black Grey	RAL 7021	Pintura electrostática com Acabamento Texturado
27230-070	553mm	500mm	1	Black Grey	RAL 7021	Pintura electrostática com Acabamento Texturado
27230-080	1000mm	1000mm	1	Black Grey	RAL 7021	Pintura electrostática com Acabamento Texturado
27230-076	900mm	900mm	1	Black Grey	RAL 7021	Pintura electrostática com Acabamento Texturado
27230-071	553mm	600mm	1	Black Grey	RAL 7021	Pintura electrostática com Acabamento Texturado

Table 2/2

Número de catálogo	Tipo
27230-072	Base Plinth
27230-070	Base Plinth
27230-080	Base Plinth
27230-076	Base Plinth
27230-071	Base Plinth

DETALHES ADICIONAIS DO PRODUTO

Please order brush strip separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE