


Slide Rail Kit



Slide Rail kit for mounting between a front and a rear pair of Slide rails, to support heavy 19" components. Side system punchings for mounting accessories and cooling components that expel to the side.

CERTIFICATIONS



CARACTERISTICAS

Slide Rail kit for mounting between a front and a rear pair of Slide rails, to support heavy 19" components

ESPECIFICAÇÕES

Product Type: Slide Rail

Material: Aço

Table 1/1

Número de catálogo	Quantidade por embalagem	Acabamento	Tipo	Works With	Certifications
22127-092	2	Aluminum-Zinc Plated			
22127-093	2	Aluminum-Zinc Plated			
23130-411	2	Aluminum-Zinc Plated			
27230-056	4	Chapa de Aço Zincada	Mounting Kit	Novastar	RoHS

Número de catálogo	Quantidade por embalagem	Acabamento	Tipo	Works With	Certifications
23130-412	10	Aluminum-Zinc Plated			

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE