

19" Front Panel for Cable Eyes

Data Solutions

19" front panel are for accommodating cable eyes.



CERTIFICATIONS



CARACTERISTICAS

19" front panel to accommodate cable eyes (to mount the eyes, insert and rotate them 45°)

ESPECIFICAÇÕES

| | |
|------------------------|-------------|
| Profundidade: | 1.5mm |
| Rack Width: | 95HP |
| Accessory Type: | Front panel |
| Product Type: | Front Panel |
| Material: | Aço |

Table 1/2

| Número de catálogo | Rack Height | Instalação | Quantidade por embalagem | Front Finish | Rear Finish | Código de cor |
|--------------------|-------------|----------------|--------------------------|--------------|-------------|---------------|
| 20118-761 | 1U | Screw-on Front | 1 | Painted | Painted | RAL 7035 |
| 20118-762 | 1U | Screw-on Front | 1 | Painted | Painted | RAL 7021 |

Table 2/2

| Número de catálogo | EMC Shielding | Acabamento | Altura | Tipo | Largura |
|--------------------|---------------|---|--------|-----------------|---------|
| 20118-761 | Não | Pintura electrostática com Acabamento Texturado | 43.6mm | 19" Front Panel | 483mm |
| 20118-762 | Não | Pintura electrostática com Acabamento Texturado | 43.6mm | 19" Front Panel | 483mm |

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE