

Dry Contact Cable

Data Solutions



Dry Contact Cable to connect I/O sensors e.g. smoke for Enlogic.

CARACTERÍSTICAS

Dry Contact Cable to connect I/O sensors e.g. smoke

1 m Cable to Sensor box with integrated magnet for easy mounting and 1.8 m connection Cable

For Enlogic

Hot pluggable for easy integration

Operating Temperature range 0 to 65 °C

ESPECIFICAÇÕES

Table 1/1

Número de catálogo	Works With	Altura	Quantidade por embalagem	Plug Type	Removable Input Cable
EA9110	RackPower	260mm	1	RJ45	Não

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE