nVent | LENTON

We connect and protect

P14 Position Coupler, Plain, European Design, 16 mm, #5, 15M

NÚMERO DE CATÁLOGO

EL16P14EE



The European Design Version (Suffix EE) is currently being phased out. All future projects should be designed with the Worldwide Design Version (Suffixes N and LN). This change is being done in order to simplify our product offering and eliminate redundant designs. Please contact Customer Care or your local Sales Engineer/Manager if you require more information on this transition.

CERTIFICATIONS

AFCAB DISPOSITIFS DE RABOUTAGE OU D'ANCRAGE D'ARMATURES DU BÉTON

KOMO®

ERICO EUROPE B.V. Tilburg Niederlande Z-1.5-200

CARACTERISTICAS

Designed to splice the same diameter bars

Designed to splice two curved, bent or straight bars, when neither bar can be rotated and where the ongoing bar is free to move in its axial direction

CARATERÍSTICAS DO PRODUTO

Número do artigo: 150390

Material: Aço

Acabamento: Plain

Versão do projeto: European (Specialty Materials)

Tamanho da viga de reforço, metric: 16 mm

Tamanho da viga de reforço, EUA: #5

Tamanho da viga de reforço, Canadá: 15M

Largura hexagonal (W): 27 mm

Comprimento 1 (L1): 102 mm

Comprimento 2 (L2): 113 mm

Bar Depth (BD): 24mm

Bar Gap 1 (BG1): 54mm

Bar Gap 2 (BG2): 65mm

Coupler Body (CB): 54mm

Peso unitário: 0.35 kg

Designed to Meet: AASHTO;ABNT NBR 8548:1984;ACI 318 Type 1 (125% Specified Yield);ACI 318 Type 2 (Specified Tensile);ACI 349;ACI 359;AS3600

DETALHES ADICIONAIS DO PRODUTO

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

Suffix "EE" has been added to some part numbers to clarify design version among regions.

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte
+1 800 753 9221
Opção 1 – Apoio ao cliente
Opção 2 – Assistência técnica

Europa
Países Baixos:
+31 800-0200135
França:
+33 800 901 793

Europa
Alemanha:
800 1890272
Outros países:
+31 13 5835404

APAC
Xangai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.