

CompacPRO Complete Desktop Case, Unshielded



The pre-configured nVent SCHROFF CompacPRO case provides electronics protection for 19" assemblies such as plug-in units and euroboards. The aluminum die cast frame and sidepanels guarantee a robust solution. In addition an extensive accessory range is available.

CERTIFICATIONS



CARACTERÍSTICAS

Desktop case pre-configured in accordance with IEC 60297-3-101 for 19" components

Aluminum construction ensures robust solution

Side panel with integrated handle function

For backplane mounting with insulation strips

Ventilation slots in rear panel

Ventilation slots in base plate

IP 20 in accordance with IEC 60529

Front and rear identical, depth-symmetrical construction

GND / earthing connections in accordance with (please see catalog page 5.76)

Conforms with DIN EN 62368-1

ESPECIFICAÇÕES

Product Type:	Case
Tipo:	Case for 19" Components

Table 1/3

Número de catálogo	Rack Height	Altura	Rack Width	Largura	Profundidade	Quantidade por embalagem
14575-155	3U	147.1mm	63HP	364mm	331mm	1
14575-174	3U	147.1mm	84HP	471mm	271mm	1
14575-156	3U	147.1mm	63HP	364mm	391mm	1
14575-135	3U	147.1mm	42HP	257mm	331mm	1
14575-114	3U	147.1mm	28HP	186mm	271mm	1
14575-136	3U	147.1mm	42HP	257mm	391mm	1
14575-178	3U	147.1mm	84HP	471mm	511mm	1
14575-134	3U	147.1mm	42HP	257mm	271mm	1
14575-115	3U	147.1mm	28HP	186mm	331mm	1
14575-154	3U	147.1mm	63HP	364mm	271mm	1
14575-175	3U	147.1mm	84HP	471mm	331mm	1
14575-176	3U	147.1mm	84HP	471mm	391mm	1

Table 2/3

Número de catálogo	Usable Height	Usable Width	Front Frame Construction	Cooling Option	Em conformidade com	EMC Shielding
14575-155	129.3mm	326mm	Single Piece	Não	IEC 60297-3-103	Não
14575-174	129.3mm	432mm	Single Piece	Não	IEC 60297-3-103	Não
14575-156	129.3mm	326mm	Single Piece	Não	IEC 60297-3-103	Não
14575-135	129.3mm	219mm	Single Piece	Não	IEC 60297-3-103	Não
14575-114	129.3mm	148mm	Single Piece	Não	IEC 60297-3-103	Não
14575-136	129.3mm	219mm	Single Piece	Não	IEC 60297-3-103	Não
14575-178	129.3mm	432mm	Single Piece	Não	IEC 60297-3-103	Não
14575-134	129.3mm	219mm	Single Piece	Não	IEC 60297-3-103	Não
14575-115	129.3mm	148mm	Single Piece	Não	IEC 60297-3-103	Não

Número de catálogo	Usable Height	Usable Width	Front Frame Construction	Cooling Option	Em conformidade com	EMC Shielding
14575-154	129.3mm	326mm	Single Piece	Não	IEC 60297-3-103	Não
14575-175	129.3mm	432mm	Single Piece	Não	IEC 60297-3-103	Não
14575-176	129.3mm	432mm	Single Piece	Não	IEC 60297-3-103	Não

Table 3/3

Número de catálogo	Acabamento	Material	Grau de proteção	Static Load
14575-155	Anodized, Pintura electrostática com Acabamento Texturado	Aluminio	IP20	30kg
14575-174	Anodized, Pintura electrostática com Acabamento Texturado	Aluminio	IP20	30kg
14575-156	Anodized, Pintura electrostática com Acabamento Texturado	Aluminio	IP20	30kg
14575-135	Anodized, Pintura electrostática com Acabamento Texturado	Aluminio	IP20	30kg
14575-114	Anodized, Pintura electrostática com Acabamento Texturado	Aluminio	IP20	30kg
14575-136	Anodized, Pintura electrostática com Acabamento Texturado	Aluminio	IP20	30kg
14575-178	Anodized, Pintura electrostática com Acabamento Texturado	Aluminio	IP20	30kg
14575-134	Anodized, Pintura electrostática com Acabamento Texturado	Aluminio	IP20	30kg

Número de catálogo	Acabamento	Material	Grau de proteção	Static Load
14575-115	Anodized, Pintura electrostática com Acabamento Texturado	Aluminio	IP20	30kg
14575-154	Anodized, Pintura electrostática com Acabamento Texturado	Aluminio	IP20	30kg
14575-175	Anodized, Pintura electrostática com Acabamento Texturado	Aluminio	IP20	30kg
14575-176	Anodized, Pintura electrostática com Acabamento Texturado	Aluminio	IP20	30kg

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE