

Interscale for Embedded NUC, Conduction Cooled, 44 x 112 x 107 mm

NÚMERO DE CATÁLOGO

14830-002



Small form factor case with integrated EMC-shielding and conduction cooling for eNUC boards, based on the innovative and flexible nVent SCHROFF Interscale platform.

CERTIFICATIONS



CARACTERÍSTICAS

Modular case consisting of 3 easy to assemble parts; body, top cover and front panel

Compliant with the SDT.03 embeddedNUC standard <http://www.sget.org/standards.html>

Cutouts specific for IES MB95 embedded NUC board (<http://en.ies.de/>)

Integrated EMC protection

Integrated heat sink on top cover with 5 mm heat fins

Rigid construction requires only two screws

Color RAL 7016

Board mounting studs installed

Other dimensions, cutout shapes or locations, and screen printing available

CARACTERÍSTICAS DO PRODUTO

Product Type: Small Form Factor Case

Família de produtos: Interscale

Tipo: Desktop

Altura: 43.7mm

Largura: 112mm

Profundidade: 106.5mm

Material: Alumínio

Cor: Anthracite Grey

Código de cor: RAL 7016

Acabamento: Pintura electrostática com Acabamento Texturado

Grau de proteção: IP20

Cooling: Conduction Cooled

Quantidade por embalagem: 1

Net Weight: 0.3kg

DETALHES ADICIONAIS DO PRODUTO

Only the listed Interscale accessories are compatible.

Modified or customized cases up on request.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE