

nVent CADDY EZ Riser, 2" Pipe

NUMĂR DE CATALOG

EZR0200



The nVent CADDY EZ Riser is a multi-purpose clamp designed to secure and support vertical pipe runs. This unified solution can be installed in several approved orientations and serves as a standard, standoff, or close-quarters riser—effectively functioning as three clamps in one. Ready-to-use out of the box, the nVent CADDY EZ Riser features pre-drilled threaded rod holes for standoff installations and score marks for simple ear removal in spaces where full-sized riser clamps do not fit.

Contractors can enjoy simplified material handling with a multi-functional clamp that allows for various orientations and retains listing even when ears are removed.

CERTIFICATIONS



CARACTERISTICI

Only one tool needed to tighten due to serrated wash-heads

Installs up to 60% faster than standard riser clamps

Integrated second set of bolt holes allow the assembly to adapt from a riser clamp into a stand-off support easily

No need to stock and use separate part families for standard and close-quarter clamps to offer a full range of listed parts

Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8)

ATRIBUTE PRODUS

Article Number: 179230

Material: Oțel

Finish: Electrogalvanized

Pipe Size: 2" Min

Outer Diameter (OD): 60.3 mm

Hole Size (HS): 9.9 mm

A: 260.4 mm

B: 177.8 mm

C: 25.4 mm

Static Load: 1100N

DETALII SUPLIMENTARE DESPRE PRODUS

Clamp is fitted for steel pipe and should be installed below a coupling or shear lug, with bolts torqued to recommended value.

Use of a socket or driver is recommended for installation.

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

