

PX NI HD Pipe Clamp w/Ext. Thread, Steel, EG, 246–252 mm OD, 3/4" Thread, 38 mm

NUMĂR DE CATALOG

PXN252EG



CARACTERISTICI

Includes male/female combination nut

Heavy duty

ATTRIBUTE PRODUS

Article Number: 577400

Nut Included: Yes

Material: Oțel

Finish: Electrogalvanized

Outer Diameter (OD): 246 - 252 mm

Rod Size (RS): M12

Gewinde (G): 3/4"

Width (W): 38 mm


Thickness (T): 2.9 mm

Screw Diameter (Sc): 8

Screw Length (L): 30mm

Static Load: 3500N

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

