

# Horizontal Adjustable Coupler



## CERTIFICATIONS



## CARACTERISTICI

Provides high-strength joint with SPEEDWAY Cable Ladder profile

Extended geometry allows greater cable ladder joint adjustments

Installs quickly and easily with included hardware

Multiple slots allow for field adjustments


## SPECIFICAȚII

Table 1/1

Număr de catalog	Article Number	Material	Finish	A	B	C
CLSW4HACGA	842020	Oțel	Hot-Dip Galvanized	190 mm	62 mm	2 mm

## DIAGRAMS

---



## AVERTIZARE

---

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

