

19" Front Panel, Vented

Data Solutions

Vented front panels allows heat dissipation through holes.



CERTIFICATIONS



CARACTERISTICI

Vented front panels (Aluminum) allows heat dissipation

SPECIFICAȚII

- Rack Width:** 95HP
- Material:** Aluminiu
- Accessory Type:** Front panel
- Product Type:** Front Panel

Table 1/2

| Număr de catalog | Rack Height | Finish | Mounting | Package Quantity | Front Finish | Rear Finish |
|------------------|-------------|----------------|----------------|------------------|--------------|-------------|
| 30118-962 | 1U | Vopsit Pulbere | Screw-on Front | 1 | Painted | Painted |
| 30702-047 | 1U | Anodized | Screw-on Front | 1 | Anodized | Anodized |
| 30702-056 | 1U | Vopsit Pulbere | Screw-on Front | 1 | Painted | Painted |

| Număr de catalog | Rack Height | Finish | Mounting | Package Quantity | Front Finish | Rear Finish |
|------------------|-------------|----------------|----------------|------------------|--------------|-------------|
| 30702-044 | 1U | Anodized | Screw-on Front | 1 | Raw | Conductive |
| 30118-963 | 2U | Anodized | Screw-on Front | 1 | Painted | Painted |
| 30702-048 | 2U | Anodized | Screw-on Front | 1 | Anodized | Anodized |
| 30702-057 | 2U | Vopsit Pulbere | Screw-on Front | 1 | Painted | Painted |
| 30118-964 | 3U | Vopsit Pulbere | Screw-on Front | 1 | Painted | Painted |
| 30702-058 | 3U | Vopsit Pulbere | Screw-on Front | 1 | Painted | Painted |
| 30702-046 | 3U | Anodized | Screw-on Front | 1 | Raw | Raw |
| 30702-045 | 2U | Anodized | Screw-on Front | 1 | Raw | Raw |
| 30702-049 | 3U | Anodized | Screw-on Front | 1 | Anodized | Anodized |

Table 2/2

| Număr de catalog | Treated Edges | Color Code | EMC Shielding | Height (H) | Type | Width (W) |
|------------------|---------------|------------|---------------|------------|-----------------|-----------|
| 30118-962 | | RAL 7021 | No | 43.6mm | 19" Front Panel | 483mm |
| 30702-047 | Yes | | No | 43.6mm | 19" Front Panel | 483mm |
| 30702-056 | | RAL 7035 | No | 43.6mm | 19" Front Panel | 483mm |
| 30702-044 | | | No | 43.6mm | 19" Front Panel | 483mm |
| 30118-963 | | RAL 7021 | No | 88.1mm | 19" Front Panel | 483mm |
| 30702-048 | Yes | | No | 88.1mm | 19" Front Panel | 483mm |
| 30702-057 | | RAL 7035 | No | 88.1mm | 19" Front Panel | 483mm |
| 30118-964 | | RAL 7021 | No | 132.5mm | 19" Front Panel | 483mm |
| 30702-058 | | RAL 7035 | No | 132.5mm | 19" Front Panel | 483mm |
| 30702-046 | | | No | 132.5mm | 19" Front Panel | 483mm |
| 30702-045 | | | No | 88.1mm | 19" Front Panel | 483mm |
| 30702-049 | Yes | | No | 132.5mm | 19" Front Panel | 483mm |

DETALII SUPLIMENTARE DESPRE PRODUS

Please order 19" assembly kit separately.

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE