

Cadweld Multi Multiple Connection Type Mold Kit

Data Solutions

NUMĂR DE CATALOG

KITCDMV01



CARACTERISTICI

Versatile mold produces a variety of connections

Patented, self-sealing system prevents weld metal leakage

Compact compression structure enables easy alignment of conductors

Language-free instruction guide

Easy-to-use system completes welds in seconds

ATRIBUTE PRODUS

Article Number: 167782

Complies With: EN IEC® 62561-1 permanent connection

Types of ERICO CADWELD MULTI Multiple Connectors							
Mold Style	Number of Battings Required	Maximum Conductor Size	Maximum Bus/Lug Size	Maximum Rebar Size, Metric	Maximum Rebar Size, US	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual
Solid or Stranded Copper Cable to Solid or Stranded Copper Cable							
SS	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
SC	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
PA	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
PA	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
XA	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
GG	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
GJ	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
GF	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
GW	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
XB	3	50 mm ² Str; 1/0 Str	-	-	-	-	-
PP	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
PK	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
GE	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
PG	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
TD	2	25 mm ² Str; #4 Str	-	-	-	-	-
TE	2	25 mm ² Str; #4 Str	-	-	-	-	-
TF	2	25 mm ² Str; #4 Str	-	-	-	-	-
Solid or Stranded Copper Cable to Rebar							
RG	2	50 mm ² Str; 1/0 Str	-	10 mm	#3	-	-
RH	2	50 mm ² Str; 1/0 Str	-	10 mm	#3	-	-
RK	2	50 mm ² Str; 1/0 Str	-	10 mm	#3	-	-
RD	3	50 mm ² Str; 1/0 Str	-	10 mm	#3	-	-
Copper or Steel Tape to Rebar							

RF	2	-	30 x 3.5 mm	10 mm	#3	-	-
Copper Tape to Copper Tape							
BB	2	-	30 x 3.5 mm	-	-	-	-
CG	3	-	30 x 3.5 mm	-	-	-	-
BG	3	-	30 x 3 mm	-	-	-	-
EB	3	-	30 x 3 mm	-	-	-	-
Solid or Stranded Copper Cable to Copper or Steel Bus/Lug							
HA	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
HC	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
HS	3	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
HT	3	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
GL	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
LA	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
LJ	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
LE	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
Galvanized Steel Tape to Galvanized Steel Tape							
BB	2	-	30 x 3 mm	-	-	-	-
CG	3	-	30 x 3 mm	-	-	-	-
Solid or Stranded Copper Cable to Ground Rods							
TG	2	10mm ² Str; #6 Str	-	-	-	1/2" - 3/4"	12.8 - 17.3 mm
GT	2	10mm ² Str; #6 Str	-	-	-	1/2" - 3/4"	12.8 - 17.3 mm
GR	2	10mm ² Str; #6 Str	-	-	-	1/2" - 3/4"	12.8 - 17.3 mm
GT	3	10mm ² Str; #6 Str	-	-	-	1/2" - 3/4"	12.8 - 17.3 mm
GR	3	10mm ² Str; #6 Str	-	-	-	1/2" - 3/4"	12.8 - 17.3 mm
Copper Tape to Ground Rod							
CN	2	-	30 x 3.5 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm
CP	2	-	30 x 3.5 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm
CN	3	-	30 x 2.5 mm - 30 x 3 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm
CP	3	-	30 x 2.5 mm - 30 x 3 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm
Galvanized Steel Tape to Ground Rod							

CN	3	-	30 x 0.5 mm - 30 x 3.5 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm
CP	3	-	30 x 0.5 mm - 30 x 3.5 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE