

Flat Braided Power Shunt, 200 mm², 500 mm

Data Solutions

NUMĂR DE CATALOG

PBC200X500



CERTIFICATIONS



CARACTERISTICI

Ideal for transformer-busduct link

Solid palms can be drilled to fit customer specific designs

Extra flexible power connection and good resistance to vibration

ATTRIBUTE PRODUS

Article Number: 564250

Material: Copper

Finish: Tinned

Wire Diameter: 0.15mm

Cross Section: 200mm²

ΔT 30 K: 550A

ΔT 50 K: 729A

Length (L): 500mm

A: 55mm

B: 50mm

C: 9mm


2 Bar Current Coefficient: 1.72

Unit Weight: 1.2kg

DETALII SUPLIMENTARE DESPRE PRODUS

When used in parallel, the two shunts must be spaced with a minimum distance equal to the thickness of the shunt to allow air cooling.

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE