

Cable to Web of Rail Complete Welder, Power, 85-141 lb T-Rail, 500 kcmil Ropelay, Right Hand

Data Solutions

NUMĂR DE CATALOG

PBWT203SRH



CARACTERISTICI

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis

Includes mold cleaner and flint ignitor

ATTRIBUTE PRODUS

Material: Graphite; Oțel; Thermoplastic

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: W

Conductor Size: 500 kcmil Ropelay

Conductor Outer Diameter, Nominal: 26.42mm

Welder Style: T20

Orientation: Right Hand

Mold Only: No

Replacement Mold: PBW3SRH

Welding Material: PB250, Sold Separately

Handle Clamp: C105C, Sold Separately

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE