

Cable to Web of Rail Complete Welder, Power, UIC60, 50 mm² Concentric, Right Hand

Data Solutions

NUMĂR DE CATALOG

PBWY301RH



CARACTERISTICI

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis

Includes mold cleaner and flint ignitor

ATTRIBUTE PRODUS

Material: Graphite; Oțel; Thermoplastic

Rail Type: UIC60

Bond Terminal Style: W

Conductor Size: 50 mm² Concentric

Conductor Outer Diameter, Nominal: 8.89mm

Welder Style: T20

Orientation: Right Hand

Mold Only: No

Replacement Mold: PBWX5LH

Welding Material: PB65, Sold Separately

Handle Clamp: C105C, Sold Separately

Conductor Sleeve: S05F, Sold Separately

Hammer Die: WD80, Sold Separately

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE