

# Compression Straight Lug, Standard, 2/0 Stranded, 70 mm<sup>2</sup> Stranded, 13 mm Hole

## Data Solutions

### NUMĂR DE CATALOG

---

**RKS7012T**



### CARACTERISTICI

---

Tin plated for corrosion prevention

Annealed copper eases the crimping operation

Optimized sizes to the most efficient electrical conductivity

Best mechanical behavior (vibration/pull-out); DIN EN 61373 Class 1B "Railway Applications"

Markings on barrel for crimping

Consistent material thickness, precise diameter and accurate cable fit; DIN46235

### ATTRIBUTE PRODUS

---

Article Number: 716656

Material: Copper

Finish: Tinned

Lug/Connector Type: Standard

Conductor Size: 2/0 Stranded; 70 mm<sup>2</sup> Stranded

Hole Size (HS): 13mm

Length (L): 59mm

Width (W): 23mm

Tool/Die Type: M2M or M2H/RKM2; M3H or M3B/RKM3; MLB/RKML

## DIAGRAMS

---



## AVERTIZARE

---

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**