We connect and protect

Outdoor Modular 20 U 1130H 2100W 900D

Data Solutions

NUMĂR DE CATALOG

10149-539

Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity. Modular contruction allows multiple configurations in size and function along with multiple cooling options.

CARACTERISTICI

- Aluminium profile frame with removable, double-walled cladding
- IP 55 or NEMA 12~
- Double-walled
- Extensive range of 19" cabinet accessories
- Access to cabinet from front, all sides possible upon request
- 100 mm high plinth, 200 and 300 mm possible
- Top cover with louvers, can be upgraded with fans or A/C unit
- RAL 7035 powder coating, other colors available upon request

ATRIBUTE PRODUS

- Product Type: Outdoor Cabinet
- Product Family: Modular
- Rack Height: 20U
- Height: 1130mm
- Width: 2100mm
- Depth: 900mm
- Wall Type: Double Walled

Door Type: Plain; Triple Door
Burglar Resistance: Optional
Cooling: Passive
EMC Shielding: Optional
Frame Material: Aluminiu
Battery Compartment: Optional
Finish: Vopsit Pulbere
Material: Aluminiu; Oțel
Mounting Setup: Optional
Package Quantity: 1
Plinth Height: 100mm

DETALII SUPLIMENTARE DESPRE PRODUS

Height dimensions are without base/plinth.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.