

Outdoor Modular 42 U 2130H 700W 600D

Data Solutions

NUMĂR DE CATALOG

10149-828



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity. Modular construction allows multiple configurations in size and function along with multiple cooling options.

CARACTERISTICI

Aluminium profile frame with removable, double-walled cladding

IP 55 or NEMA 12~

Double-walled

Extensive range of 19" cabinet accessories

Access to cabinet from front, all sides possible upon request

100 mm high plinth, 200 and 300 mm possible

Top cover with louvers, can be upgraded with fans or A/C unit

RAL 7035 powder coating, other colors available upon request

ATTRIBUTE PRODUS

Product Type: Outdoor Cabinet

Product Family: Modular

Rack Height: 42U

Height: 2130mm

Width: 700mm

Depth: 600mm

Wall Type: Double Walled

Door Type: Plain; Single Door

Burglar Resistance: Optional

Cooling: Passive

EMC Shielding: Optional

Battery Compartment: Optional

Finish: Vopsit Pulbere

Frame Material: Aluminiu

Material: Aluminiu; Oțel

Mounting Setup: Optional

Package Quantity: 1

Plinth Height: 100mm

DETALII SUPLIMENTARE DESPRE PRODUS

Height dimensions are without base/plinth.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE