

Varistar CP Steel Door, Perforated With 1-Point Locking, RAL 7021, 42 U, 2000H, 800W

Data Solutions

NUMĂR DE CATALOG

21630-013



Varistar CP Perforated Steel Door, IP 20 with Single Point Locking.

CARACTERISTICI

Perforated steel door with single point locking for IP 20 protection class

Opening angle 180°

Key lock cover

ATRIBUTE PRODUS

Rack Height: 42U

Height: 2000mm

Width: 800mm

Locking Type: Single Point Locking

Package Quantity: 1

Color: Black Grey

Color Code: RAL 7021

Complies With: IEC 61587-1; IEC 61587-3

Material: Oțel

Product Family: Varistar CP

Product Type: Cabinet Door

Protection Rating: IP20

Type: Steel Door, Perforated

Works With: Varistar CP

Net Weight: 18.86kg

DETALII SUPLIMENTARE DESPRE PRODUS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE