

Varistar CP Steel Door, Perforated With 3-Point Locking, RAL 7021, 52 U, 2450H, 600W

Data Solutions

NUMĂR DE CATALOG

21630-100



Varistar CP perforated steel door, IP 20 with three point locking.

CARACTERISTICI

Perforated steel door with three point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

ATRIBUTE PRODUS

Rack Height: 52U

Height: 2450mm

Width: 600mm

Package Quantity: 1

Color: Black Grey

Color Code: RAL 7021

Complies With: IEC 61587-1; IEC 61587-3

Finish: Vopsit Pulbere

Locking Type: 3-Point Locking

Material: Oțel

Product Family: Varistar CP

Product Type: Cabinet Door

Protection Rating: IP20

Type: Steel Door, Perforated

Works With: Varistar CP

Net Weight: 13.261kg

DETALII SUPLIMENTARE DESPRE PRODUS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE