

Varistar CP Glazed Door With 3-Point Locking, RAL 7021, 42 U, 2000H 600W, IP55

Data Solutions

NUMĂR DE CATALOG

21630-725



Glazed door with 3 point locking allows stronger contact between door and the cabinet frame.

CARACTERISTICI

Glazed Door With 3-Point Locking, With Lock

Lever handle with key insert (2 keys)

Opening angle 180°

Security glass, 6 mm

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

ATTRIBUTE PRODUS

Rack Height: 42U

Height: 2000mm

Width: 600mm

Protection Rating: IP55

Package Quantity: 1

Color: Black Grey

Color Code: RAL 7021

Complies With: IEC 61587-1

Finish: Vopsit Pulbere

Locking Type: 3-Point Locking

Material: Oțel; Glass

Product Family: Varistar CP

Product Type: Cabinet Door

Type: Glass Door

Works With: Varistar CP

Net Weight: 22.836kg

DETALII SUPLIMENTARE DESPRE PRODUS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE