

19" Front Panel, 7 U, 3 mm, Al, RAL7035

Data Solutions

NUMĂR DE CATALOG

30118-306



Front panels made of Aluminum.

CERTIFICATIONS



CARACTERISTICI

Aluminum, 4 or 3 mm thick, with Anodized or Painted finish

ATTRIBUTE PRODUS

Rack Height: 7U

Depth (D): 3mm

Accessory Type: Front panel

Mounting: Screw-on Front

Finish: Vopsit Pulbere

Front Finish: Painted

Package Quantity: 1

Color Code: RAL 7035

Height (H): 310.3mm

Product Type: Front Panel

Rack Width: 95HP

Type: 19" Front Panel

Width (W): 483mm

Gross Weight: 1.245kg

Please order 19" assembly kit separately.

Technical drawing of a rectangular plate with dimensions and hole positions. The plate has a width of 483 and a height of H. There are four holes along the top edge, with a center-to-center distance of 465 between the first and last holes. The distance from the left edge to the center of the first hole is g. The distance from the center of the first hole to the center of the second hole is x1. The distance from the center of the second hole to the center of the third hole is x2. The distance from the center of the third hole to the center of the fourth hole is x1. The distance from the center of the fourth hole to the right edge is g.

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE