

# Extention Connector/Cable Assembly, for LED Light 1M

## Data Solutions

### NUMĂR DE CATALOG

**57273**



The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

### CERTIFICATIONS



### CARACTERISTICI

Power cable for LED light mounting into cabinet

Lights can be easily mounted vertically or horizontally

Simple through-wiring based on a plug-and-play system

### ATRIBUTE PRODUS

Input Voltage AC: 250V max

Accessory Type: Lights

Protection Rating: IP20

Length: 1000mm

Package Quantity: 1

Color: Black

Finish: Smooth

Material: Plastic

Product Type: Light

Type: Connection Cable

Connection Type: Infeed; Trough-Wiring; 2-Pole

Nominal Voltage: 250V

Operating Temperature: 60°C min

Rated Current: 10A

Weight: 0.3kg

## AVERTIZARE

---

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**