

Monitor, Keyboard, Touchpad, 1 U Drawer, Reduced Depth, French Keyboard

Data Solutions

NUMĂR DE CATALOG

60118-585



Designed for standard 19" rackmount designed for comfort
robust design for heavy use or harsh environment operation

CERTIFICATIONS



CARACTERISTICI

Pull-out 17" TFT color monitor chassis, 1 U (resolution Full HD; connects to VGA or DVI-D interface)

Keyboard with different keyboard layout (connects via USB)

Integral touchpad (connects via USB)

Voltage supply: Wide-range input (nominal mains voltage 110 to 240 VAC), Voltage supply 12, 24 and 48 VDC on request

Depth-adjustable mounting for different pitches of server panel/slide mounts; Mounting depth (dimension c = spacing of 19" profiles): dimension c 450 ... 640 mm

With DVI connection

ATTRIBUTE PRODUS

Rack Height: 1U

Color: Jet Black

Color Code: RAL 9005

Depth: 400mm

Product Type: Cabinet/Rack Drawer

Type: Monitor, Keyboard, Touchpad

Works With: 19" Cabinets

Keyboard Type: AZERTY

Net Weight: 13.4kg

DETALII SUPLIMENTARE DESPRE PRODUS

Further versions on request – With trackball or numeric pad.

Other Keyboard layouts see user manual.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE