

Basic PDU, EB0321, 230 VAC, 1-PH, 32 A

Data Solutions

NUMĂR DE CATALOG

EB0321



Modular, compact PDU. Ultra-Low Profile Design

CARACTERISTICI

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 230 VAC, 1-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

ATTRIBUTE PRODUS

Product Family: Enlogic

Type: Basic PDU

Product Type: Socket Strip

Socket Type: (20) C13

Socket Quantity: 20

Color: Black

Circuit Breaker: 16 A, 1-pole, Hy-Mag

Switched Outlets: No

Circuit Breaker Quantity: 2

Power Rating: 7.4 kVA

Input Cable Location: Top Feed

Input Voltage: 200 – 240V

Phase: 1 PH

Interrupt Rating: 5kAIC

Max Power Input: 7.44 kVA

Nominal Voltage: 230V

On/Off Switch Included: No

Output Voltage: 230VAC

Amperage (Derated Amperage): 32 A

Plug Type: IEC 60309 332P6 (IP44)

Rack Units: 0U

Removable Input Cable: No

Metering Type: None

Material: Oțel

Finish: Vopsit Pulbere

Height: 817mm

Width: 52mm

Depth: 53mm

Weight: 5.61kg

Package Quantity: 1

Input Cable Length: 3m

DETALII SUPLIMENTARE DESPRE PRODUS

Please order bracket for vertical mounting separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE