

MS PDU, 0U, 100A(80A)NA/100A Int, 380-415V, 3P Wye, 24 CB, 48 Locking Combo

Data Solutions

NUMĂR DE CATALOG

EN2990

The Advantage Series Input Metered, Outlet Switched PDU family offers energy metering with advanced power and environmental monitoring options and remote outlet on/off switching. Comprehensive monitoring at both the input phase and circuit breaker levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

CARACTERISTICI

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information

UL 2900-1 certified for safety software cybersecurity for network-connectable products

Dual network connectivity ports: 1x Gigabit Ethernet (10/100/1000 Mbps) and 1x (10/100 Mbps) connection/IP address

Ethernet cascading up to 64 PDUs. Each PDU can provide DC power sufficient to power network management electronics

Dual Ethernet ports for redundant network communications

Remote connectivity through HTTP(s), IPv4 and IPv6, SSH, Virtual Serial, SNMP (v1, v2c, v3), JSON-RPC, LDAP(S)

Data efficient REACT framework with native mobile device support

Tool-less hot swappable Network Management Card (NMC) with Cortex A-5 for microprocessing and memory that can be installed both upright and upside down for top or bottom power inputs

The border color of the NMC display is user programmable for power source identification by PDU

The NMC supports up to 10 digital sensors for environmental and/or electronic lock monitoring

Display languages include English, Spanish, German, French, Italian, Korean, Japanese, and Chinese (simplified)

ATTRIBUTE PRODUS

Product Family: Enlogic

Type: Intelligent PDU

Product Type: Socket Strip

Socket Type: (24) Locking C13/C15; (24) Locking C13/C15/C19/C21

Socket Quantity: 48

Color: Black

Switched Outlets: Yes

Cable Length: 1800mm

Circuit Breaker: 20 A, 1-pole, Hy-MagA

Power Rating: 57.6 kVA North America; 69 kVA International

Circuit Breaker Quantity: 24

Nominal Power Output: 230VAC

Nominal Voltage: 415V

On/Off Switch Included: Yes

Amperage (Derated Amperage): 100 A (80 A) North America; 100 A International

Output Voltage: 208 – 230VAC

Rack Units: 0U

Plug Type: IEC 60309 5125P6W (IP67)

Metering Type: Input

Removable Input Cable: No

Material: Oțel

Finish: Vopsit Pulbere

Height: 2030mm

Width: 85mm

Depth: 85mm

Package Quantity: 1

Input Cable Length: 1.8m

DETALII SUPLIMENTARE DESPRE PRODUS

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE