

Varistar CP Base/Plinth

Data Solutions

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.



CARACTERISTICI

2 support profiles, for front and rear

Static load-carrying capacity 1000 kg

SPECIFICAȚII

Product Type: Cabinet/Rack Base

Material: Oțel

Table 1/2

Număr de catalog	Height	Width	Package Quantity	Color	Color Code	Depth
24630-037	200mm	800mm	1	Black Grey	RAL 7021	
24630-034	100mm	600mm	1	Black Grey	RAL 7021	600mm
24630-066	200mm	600mm	1	Black Grey	RAL 7021	
24630-035	100mm	800mm	1	Black Grey	RAL 7021	
24630-065	100mm	800mm	1	Black Grey	RAL 7021	
24630-064	100mm	600mm	1	Black Grey	RAL 7021	
24630-036	200mm	600mm	1	Black Grey	RAL 7021	
24630-067	200mm	800mm	1	Black Grey	RAL 7021	

Table 2/2

Număr de catalog	Finish	Type
24630-037	Vopsit Pulbere	Base Plinth, Perforated
24630-034	Vopsit Pulbere	Base Plinth, Perforated
24630-066	Vopsit Pulbere	Base Plinth, Plain
24630-035	Vopsit Pulbere	Base Plinth, Perforated
24630-065	Vopsit Pulbere	Base Plinth, Plain
24630-064	Vopsit Pulbere	Base Plinth, Plain
24630-036	Vopsit Pulbere	Base Plinth, Perforated
24630-067	Vopsit Pulbere	Base Plinth, Plain

DETALII SUPLIMENTARE DESPRE PRODUS

Please order side trims separately.

Cannot be used in conjunction with castors

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE