

# 19" Cable Ducting

19" unit for easy and effective cable management (cable ducting).



## CERTIFICATIONS



## CARACTERISTICI

19" Front panel for cable ducting

## SPECIFICAȚII

**Accessory Type:** Front panel  
**Product Type:** Front Panel  
**Material:** Oțel

Table 1/3

Număr de catalog	Rack Height	Mounting	Package Quantity	Front Finish	Rear Finish	Color Code
20118-734	1U	Screw-on Front	1	Painted	Painted	RAL 7035
20118-767	1U	Screw-on Front	1	Painted	Painted	RAL 7021
20118-736	2U	Screw-on Front	1	Painted	Painted	RAL 7035
20118-768	2U	Screw-on Front	1	Anodized	Conductive	RAL 7021

Table 2/3

Număr de catalog	Depth	EMC Shielding	Finish	Height	Rack Width	Type
20118-734	1.5mm	No	Vopsit Pulbere	43.6mm	95HP	19" Front Panel
20118-767	1.5mm	No	Vopsit Pulbere	43.6mm	95HP	19" Front Panel
20118-736	1.5mm	No	Vopsit Pulbere	88.1mm	95HP	19" Front Panel
20118-768	1.5mm	No	Vopsit Pulbere	88.1mm	95HP	19" Front Panel

Table 3/3

Număr de catalog	Width
20118-734	483mm
20118-767	483mm
20118-736	483mm
20118-768	483mm

## DETALII SUPLIMENTARE DESPRE PRODUS

Please order 19" assembly kit separately.

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Portofoliul nostru puternic de mărci:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**