

19" Drawer



19" Drawers allow mounting of laptops, writing surfaces for easy operations. The SCHROFF 19" drawer has a load capacity of 15 KG, allowing a wide range of products to be assembled into the drawer.

CERTIFICATIONS



CARACTERISTICI

Static load-carrying capacity 15 kg

Optional writing surface

SPECIFICAȚII

- Static Load:** 15kg
- Product Type:** Cabinet/Rack Drawer
- Material:** Oțel

Table 1/2

Număr de catalog	Rack Height	Finish	Package Quantity	Color	Color Code	Front Finish
20110-054	1U	Vopsit Pulbere	1	Light Grey	RAL 7035	
20110-061	1U	Vopsit Pulbere	1			Anodized
20110-180	1U	Vopsit Pulbere	1	Black Grey	RAL 7021	
20110-056	3U	Vopsit Pulbere	1	Light Grey	RAL 7035	
20110-062	2U	Vopsit Pulbere	1			Anodized

Număr de catalog	Rack Height	Finish	Package Quantity	Color	Color Code	Front Finish
20110-181	2U	Vopsit Pulbere	1	Black Grey	RAL 7021	
20110-063	3U	Vopsit Pulbere	1			Anodized
20110-055	2U	Vopsit Pulbere	1	Light Grey	RAL 7035	
20110-182	3U	Vopsit Pulbere	1	Black Grey	RAL 7021	

Table 2/2

Număr de catalog	Type	Works With
20110-054	Drawer	19" Cabinets
20110-061	Drawer	19" Cabinets
20110-180	Drawer	19" Cabinets
20110-056	Drawer	19" Cabinets
20110-062	Drawer	19" Cabinets
20110-181	Drawer	19" Cabinets
20110-063	Drawer	19" Cabinets
20110-055	Drawer	19" Cabinets
20110-182	Drawer	19" Cabinets

DETALII SUPLIMENTARE DESPRE PRODUS

Please order 19" assembly kit separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE