

# CompacPRO Desktop Case, Unshielded



The nVent SCHROFF CompacPRO case provides electronics protection for 19" and individual electronic assemblies. The aluminum die cast frame and profile sidepanels guarantee a robust solution. In addition an extensive accessory range is available.

## CERTIFICATIONS



## CARACTERISTICI

Desktop case for individual assembly

Aluminum construction ensures robust solution

International dimensions in accordance with IEC 6297-3-101

Side panel with integrated handle function

Front and rear identical, depth-symmetrical construction

Ventilation slots in base plate

IP 20 in accordance with IEC 60529

## SPECIFICAȚII

- Product Type:** Case
- Type:** Case for Individual Electronic Components
- Product Family:** CompacPRO

Table 1/2

Număr de catalog	Rack Height	Height	Rack Width	Width	Depth	Package Quantity

14575-465	6U	280.5mm	84HP	471mm	331mm	1
14575-145	3U	147.1mm	63HP	364mm	331mm	1
14575-269	4U	191.6mm	84HP	471mm	451mm	1
14575-025	2U	102.6mm	42HP	257mm	331mm	1
14575-245	4U	191.6mm	63HP	364mm	331mm	1
14575-171	3U	147.1mm	84HP	471mm	511mm	1
14575-165	3U	147.1mm	84HP	471mm	331mm	1
14575-125	3U	147.1mm	42HP	257mm	331mm	1
14575-147	3U	147.1mm	63HP	364mm	391mm	1
14575-469	6U	280.5mm	84HP	471mm	451mm	1
14575-123	3U	147.1mm	42HP	257mm	271mm	1
14575-127	3U	147.1mm	42HP	257mm	391mm	1
14575-247	4U	191.6mm	63HP	364mm	391mm	1
14575-169	3U	147.1mm	84HP	471mm	451mm	1
14575-447	6U	280.5mm	63HP	364mm	391mm	1
14575-265	4U	191.6mm	84HP	471mm	331mm	1
14575-063	2U	102.6mm	84HP	471mm	271mm	1
14575-067	2U	102.6mm	84HP	471mm	391mm	1
14575-445	6U	280.5mm	63HP	364mm	331mm	1
14575-027	2U	102.6mm	42HP	257mm	391mm	1

Table 2/2

Număr de catalog	Rack Height	Height	Rack Width	Width	Depth	Package Quantity
14575-167	3U	147.1mm	84HP	471mm	391mm	1
14575-467	6U	280.5mm	84HP	471mm	391mm	1
14575-463	6U	280.5mm	84HP	471mm	271mm	1
14575-223	4U	191.6mm	42HP	257mm	271mm	1
14575-065	2U	102.6mm	84HP	471mm	331mm	1
14575-103	3U	147.1mm	28HP	186mm	271mm	1
14575-471	6U	280.5mm	84HP	471mm	511mm	1
14575-163	3U	147.1mm	84HP	471mm	271mm	1
14575-023	2U	102.6mm	42HP	257mm	271mm	1
14575-105	3U	147.1mm	28HP	186mm	331mm	1
14575-267	4U	191.6mm	84HP	471mm	391mm	1
14575-271	4U	191.6mm	84HP	471mm	511mm	1
14575-143	3U	147.1mm	63HP	364mm	271mm	1

Număr de catalog	Rack Height	Height	Rack Width	Width	Depth	Package Quantity
14575-243	4U	191.6mm	63HP	364mm	271mm	1
14575-225	4U	191.6mm	42HP	257mm	331mm	1

Table 1/2

Număr de catalog	Usable Height	Usable Width	Front Frame Construction	Cooling Option	Complies With	EMC Shielding
14575-465	262.9mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-145	129.3mm	326mm	Single Piece	No	IEC 60297-3-103	No
14575-269	173.8mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-025	84.4mm	219mm	Single Piece	No	IEC 60297-3-103	No
14575-245	173.8mm	326mm	Single Piece	No	IEC 60297-3-103	No
14575-171	129.3mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-165	129.3mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-125	129.3mm	219mm	Single Piece	No	IEC 60297-3-103	No
14575-147	129.3mm	326mm	Single Piece	No	IEC 60297-3-103	No
14575-469	262.9mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-123	129.3mm	219mm	Single Piece	No	IEC 60297-3-103	No
14575-127	129.3mm	219mm	Single Piece	No	IEC 60297-3-103	No
14575-247	173.8mm	326mm	Single Piece	No	IEC 60297-3-103	No
14575-169	129.3mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-447	262.9mm	326mm	Single Piece	No	IEC 60297-3-103	No
14575-265	173.8mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-063	84.4mm	432mm	Single Piece	No	IEC 60297-3-103	No

<b>Număr de catalog</b>	<b>Usable Height</b>	<b>Usable Width</b>	<b>Front Frame Construction</b>	<b>Cooling Option</b>	<b>Complies With</b>	<b>EMC Shielding</b>
14575-067	84.4mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-445	262.9mm	326mm	Single Piece	No	IEC 60297-3-103	No
14575-027	84.4mm	219mm	Single Piece	No	IEC 60297-3-103	No

Table 2/2

<b>Număr de catalog</b>	<b>Usable Height</b>	<b>Usable Width</b>	<b>Front Frame Construction</b>	<b>Cooling Option</b>	<b>Complies With</b>	<b>EMC Shielding</b>
14575-167	129.3mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-467	262.9mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-463	262.9mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-223	173.8mm	219mm	Single Piece	No	IEC 60297-3-103	No
14575-065	84.4mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-103	129.3mm	148mm	Single Piece	No	IEC 60297-3-103	No
14575-471	262.9mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-163	129.3mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-023	84.4mm	219mm	Single Piece	No	IEC 60297-3-103	No
14575-105	129.3mm	148mm	Single Piece	No	IEC 60297-3-103	No
14575-267	173.8mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-271	173.8mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-143	129.3mm	326mm	Single Piece	No	IEC 60297-3-103	No
14575-243	173.8mm	326mm	Single Piece	No	IEC 60297-3-103	No
14575-225	173.8mm	219mm	Single Piece	No	IEC 60297-3-103	No

Table 1/2

Număr de catalog	Finish	Material	Protection Rating	Static Load
14575-465	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-145	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-269	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-025	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-245	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-171	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-165	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-125	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-147	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-469	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-123	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-127	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-247	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-169	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-447	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-265	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-063	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-067	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-445	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-027	Vopsit Pulbere	Aluminiu	IP20	30kg

Table 2/2

Număr de catalog	Finish	Material	Protection Rating	Static Load
14575-167	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-467	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-463	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-223	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-065	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-103	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-471	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-163	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-023	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-105	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-267	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-271	Vopsit Pulbere	Aluminiu	IP20	30kg

Număr de catalog	Finish	Material	Protection Rating	Static Load
14575-143	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-243	Vopsit Pulbere	Aluminiu	IP20	30kg
14575-225	Vopsit Pulbere	Aluminiu	IP20	30kg

## DETALII SUPLIMENTARE DESPRE PRODUS

GND / earthing connections in accordance with

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Portofoliul nostru puternic de mărci:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**