

CPCI Backplane

The nVent SCHROFF CompactPCI Backplanes have best in class signal integrity and MTBF values due to SMD components, ceramics capacitors and press fit connectors.



CERTIFICATIONS



CARACTERISTICI

Digital GND can be connected to/isolated from chassis GND by means of screws

V(I/O) can be set to +3.3 V or +5 V

Outer layers act as GND surfaces

Utility plug for status signals (SMCQ)

Outstanding high frequency noise suppression and very high MTBF values due to ceramic capacitors

Intelligent platform management bus (IPMB) connector to PICMG 2.9

SPECIFICAȚII

Table 1/2

Număr de catalog	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23006-794	Backplane	2	9U	CompactPCI, 64-bit	Left	4HP
23006-799	Backplane	4	7U	CompactPCI, 64-bit	Left	4HP
23006-798	Backplane	6	7U	CompactPCI, 64-bit	Left	4HP

Număr de catalog	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23006-797	Backplane	8	9U	CompactPCI, 64-bit	Left	4HP
23006-796	Backplane	6	9U	CompactPCI, 64-bit	Left	4HP
23006-795	Backplane	4	7U	CompactPCI, 64-bit	Left	4HP
23006-793	Backplane	2	7U	CompactPCI, 64-bit	Left	4HP
23006-792	Backplane	2	7U	CompactPCI, 64-bit	Left	4HP
23006-611	Backplane	8	9U	CompactPCI, 64-bit, PSB, H.110 Bus	Left	4HP
23006-601	Backplane	8	6U	CompactPCI, 64-bit, H.110 Bus	Right	4HP

Table 2/2

Număr de catalog	Voltage I/O	Connector Type	Power Connector Type	Utility Connector Type	Width	Package Quantity
23006-794	5V	HM 2.0	(1) P47	SMCQ, 12-pin	39.64mm	1
23006-799	5V	HM 2.0	Mini-fit 24-pin	SMCQ, 12-pin		1
23006-798	5V	HM 2.0	Mini-fit 24-pin	SMCQ, 12-pin	121mm	1
23006-797	5V	HM 2.0	(2) P47	SMCQ, 12-pin	161.56mm	1
23006-796	5V	HM 2.0	(2) P47	SMCQ, 12-pin	121mm	1
23006-795	5V	HM 2.0	(2) P47	SMCQ, 12-pin		1
23006-793	5V	HM 2.0	Mini-fit 10-pin	SMCQ, 12-pin	39.64mm	1
23006-792	5V	HM 2.0	ATX (male) Connector		39.64mm	1
23006-611	5V	HM 2.0	(2) P47	SMCQ, 12-pin	161.56mm	1
23006-601	5V	HM 2.0	Power Bugs for M4 Cable Lugs	SMCQ, 12-pin	161.56mm	1

DETALII SUPLIMENTARE DESPRE PRODUS

Other configurations available on request.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE