

Horizontal Rail, Front, Type R-LD, Rugged, Long Lip , 40 HP

NUMĂR DE CATALOG

34566-340



Combinations of horizontal rails and side panels

„+“ can be combined, „-“ combination not recommended

	Light 1	Flexibel 2	Heavy 3 HP	Rugged 4 HP
Horizontal rail	-	+	+	+
Horizontal rail	+	+	+	+
Horizontal rail	+	+	-	-
Horizontal rail	+	+	-	-
Side panel	+	+	-	-

Light 1, Flexibel 2, Heavy 3 HP, Rugged 4 HP

The rugged horizontal rail type can handle shock and vibration up to 25 g. It enables the use of IEEE handles.

CERTIFICATIONS



CARACTERISTICI

Type R-LD "rugged" horizontal rails with 3-hole fixing for increased robustness

For insertion/extraction of CompactPCI or, VME64x boards

With HP units printed from 28 HP upwards

Length 20, 28, 40, 42, 63, 84 HP or 1000 mm

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

ATTRIBUTE PRODUS

Rack Width: 40HP

Package Quantity: 1

Finish: Anodized

Length: 208.28mm

Material: Aluminiu

Product Family: EuropacPRO

Product Type: Horizontal Rail

Type: Rugged, LD

Works With: Subracks

Gross Weight: 0.131kg

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE