

# PropacPRO Complete Desktop Case, Shielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" assemblies such as plug-in units and euroboards. The aluminum die cast frames and profile sidepanels guarantee a robust solution. The case includes EMC shielding as standard.

## CERTIFICATIONS



## CARACTERISTICI

Desktop case, pre-configured in accordance with IEC 60297-3-101 for 19" components

Shielded

Ventilation slots in base plate

Rear panel with vent slots

IP 20 in accordance with IEC 60529

Conforms with DIN EN 62368-1

## SPECIFICAȚII

<b>Static Load:</b>	25kg
<b>Product Type:</b>	Case
<b>Type:</b>	Case for 19" Components
<b>Product Family:</b>	PropacPRO
<b>EMC Shielding:</b>	Yes

Table 1/3

Număr de catalog	Rack Height	Rack Width	Depth	Package Quantity	Usable Height	Usable Width
------------------	-------------	------------	-------	------------------	---------------	--------------

24576-122	6U	84HP	446mm	1	245.7mm	432mm
24576-105	3U	42HP	386mm	1	112.3mm	219mm
24576-102	3U	28HP	326mm	1	112.3mm	148mm
24576-110	3U	84HP	326mm	1	112.3mm	432mm
24576-111	3U	84HP	386mm	1	112.3mm	432mm
24576-121	6U	84HP	326mm	1	245.7mm	432mm
24576-104	3U	42HP	326mm	1	112.3mm	219mm
24576-106	3U	63HP	266mm	1	112.3mm	326mm
24576-109	3U	84HP	266mm	1	112.3mm	432mm
24576-112	3U	84HP	446mm	1	112.3mm	432mm
24576-113	3U	84HP	506mm	1	112.3mm	432mm
24576-103	3U	42HP	266mm	1	112.3mm	219mm
24576-107	3U	63HP	326mm	1	112.3mm	326mm
24576-101	3U	28HP	266mm	1	112.3mm	148mm
24576-108	3U	63HP	386mm	1	112.3mm	326mm

Table 2/3

Număr de catalog	Front Frame Construction	Cooling Option	Complies With	Finish	Height	Material
24576-122	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	289mm	Aluminiu
24576-105	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-102	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-110	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-111	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-121	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	289mm	Aluminiu
24576-104	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-106	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-109	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-112	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu

Număr de catalog	Front Frame Construction	Cooling Option	Complies With	Finish	Height	Material
24576-113	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-103	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-107	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-101	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-108	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu

Table 3/3

Număr de catalog	Protection Rating	Width
24576-122	IP20	470.3mm
24576-105	IP20	257mm
24576-102	IP20	185.9mm
24576-110	IP20	470.3mm
24576-111	IP20	470.3mm
24576-121	IP20	470.3mm
24576-104	IP20	257mm
24576-106	IP20	363.7mm
24576-109	IP20	470.3mm
24576-112	IP20	470.3mm
24576-113	IP20	470.3mm
24576-103	IP20	257mm
24576-107	IP20	363.7mm
24576-101	IP20	185.9mm
24576-108	IP20	363.7mm

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



Portofoliul nostru puternic de mărci:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**