


# PropacPRO 机箱装饰条

用于打造个性化 PropacPRO 机箱设计。可从压铸框架后侧用螺钉固定构件。



## 认证



## 功能

个性化机箱设计

可提供 3 种样式和两种颜色

## 技术参数

材料: 铝  
 完成: 阳极氧化  
 搭配: 仪器箱  
 产品类型: 角型材  
 产品系列: PropacPRO

Table 1/1

物料号	机架宽度	类型	颜色代码	颜色
20850-299	42HP	圆形	RAL 5007	亮蓝色
20850-196	42HP	三角形	RAL 7035	浅灰色

物料号	机架宽度	类型	颜色代码	颜色
20850-190	42HP	方形	RAL 7035	浅灰色
20850-315	42HP	方形	RAL 5007	亮蓝色
20850-184	42HP	圆形	RAL 7035	浅灰色
20850-331	42HP	三角形	RAL 5007	亮蓝色
20850-185	63HP	圆形	RAL 7035	浅灰色
20850-191	63HP	方形	RAL 7035	浅灰色
20850-197	63HP	三角形	RAL 7035	浅灰色
20850-316	63HP	方形	RAL 5007	亮蓝色
20850-332	63HP	三角形	RAL 5007	亮蓝色
20850-300	63HP	圆形	RAL 5007	亮蓝色
20850-192	84HP	方形	RAL 7035	浅灰色
20850-198	84HP	三角形	RAL 7035	浅灰色
20850-186	84HP	圆形	RAL 7035	浅灰色
20850-317	84HP	方形	RAL 5007	亮蓝色
20850-333	84HP	三角形	RAL 5007	亮蓝色
20850-301	84HP	圆形	RAL 5007	亮蓝色

## 其他产品详情

可应要求提供 28 HP 尺寸和更多颜色。

不能与前罩结合。

## 警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



我们强大的品牌组合:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**