


Adjustable Vented Shelf, fits 19 in., Black, Steel

Data Solutions

CATALOG NUMBER

ESHVA19



The Adjustable Steel Vented Shelf is adjustable from front to back in 25-mm increments. It is designed to support networking equipment within an open-frame rack. The shelf mounts to either the front or rear flange of an open-frame rack. The shelf's load rating is 60 lb. (27.2 kg)

FEATURES

The Adjustable Steel Vented Shelf is adjustable from front to back in 25-mm increments

It is designed to support networking equipment within an open-frame rack

The shelf mounts to either the front or rear flange of an open-frame rack

The shelf's load rating is 60 lb. (27.2 kg)

PRODUCT ATTRIBUTES

Article Number: 21829

Material: Mild Steel

Finish: Powder Coated

Color: Jet Black

Color Code: RAL 9005

Thickness: 1.52mm

Rack Units: 2U

Width: 10922mm

Height: 89mm

Depth: 400mm

Rack Width: 19in

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE