

19" Assembly Kit M6

Data Solutions



For standard grounding use a grounding nut and washer on at least one attachment point.

When 19" assembly kit is used with conductive 19" panel mount, grounding cage nuts are not needed.

CERTIFICATIONS



VLASTNOSTI

Assembly kits for assembly of 19" components into a cabinet

For mounting of front panels, distribution fields or other components on the frame, slide mounts or depth members with square cut-outs

SPECIFIKACE

Product Type: Assembly Kit

Povrchová úprava: Pozinkovaná Ocel

Table 1/2

| Katalogové číslo | Length | Množství v balení | Thread Size | Materiál | Produktová řada | Typ |
|------------------|--------|-------------------|-------------|----------|-----------------|-----|
|------------------|--------|-------------------|-------------|----------|-----------------|-----|

| | | | | | | |
|-----------|------|-----|----|-----------|---|-------------------------|
| 21190-095 | | 4 | M6 | Ocel, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor | Mounting Kit |
| 21120-213 | | 4 | M6 | Ocel | | Mounting Kit |
| 21120-196 | 16mm | 4 | M6 | Ocel | | Mounting Kit, Grounding |
| 21100-435 | | 8 | M6 | Ocel, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor | Mounting Kit |
| 21120-199 | 13mm | 100 | M6 | Ocel | | Mounting Kit, Grounding |
| 21120-198 | 16mm | 50 | M6 | Ocel | | Mounting Kit, Grounding |
| 21120-197 | 16mm | 32 | M6 | Ocel | | Mounting Kit, Grounding |
| 21190-435 | | 32 | M6 | Ocel, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor | Mounting Kit |

| | | | | | | |
|-----------|--|-----|----|-----------|---|--------------|
| 21101-810 | | 100 | M6 | Ocel, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor | Mounting Kit |
| 21101-809 | | 50 | M6 | Ocel, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor | Mounting Kit |
| 21120-215 | | 32 | M6 | Ocel | | Mounting Kit |
| 21120-214 | | 50 | M6 | Ocel | | Mounting Kit |
| 21120-216 | | 100 | M6 | Ocel | | Mounting Kit |

Table 2/2

| Katalogové číslo | Works With | Certifications |
|------------------|---|----------------|
| 21190-095 | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS |
| 21120-213 | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | |
| 21120-196 | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | |
| 21100-435 | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS |
| 21120-199 | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | |
| 21120-198 | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | |
| 21120-197 | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | |
| 21190-435 | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS |
| 21101-810 | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS |

| Katalogové číslo | Works With | Certifications |
|------------------|---|----------------|
| 21101-809 | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS |
| 21120-215 | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | |
| 21120-214 | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | |
| 21120-216 | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | |

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE