

Interscale Desktop Case, Perforated



Flexible desktop case with integrated EMC protection and perforated sides. Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.

CERTIFICATIONS



VLASTNOSTI

Modular desktop case consisting of 4 assembled parts

Developed according to IEC 60297-3-109 (under progress at IEC)

Integrated EMC protection

Ingress protection up to IP 20

Color RAL 7016

Modified or customized cases upon request

SPECIFIKACE

Materiál:	Hliník; Ocel
Typ:	Desktop
Produktová řada:	Interscale
Stupeň krytí:	IP20
Kód barvy:	RAL 7016
Product Type:	Small Form Factor Case

Table 1/2

Katalogové číslo	Výška	Množství v balení	Šířka	Hloubka	Cooling	Barva
14825-154	43.7mm	1	221mm	177mm	Perforated	Anthracite Grey
14825-254	88.1mm	1	221mm	177mm	Perforated	Anthracite Grey
14825-255	88.1mm	1	221mm	221mm	Perforated	Anthracite Grey
14825-197	43.7mm	1	399mm	310mm	Perforated	Anthracite Grey
14825-275	88.1mm	1	310mm	221mm	Perforated	Anthracite Grey
14825-195	43.7mm	1	399mm	221mm	Perforated	Anthracite Grey
14825-295	88.1mm	1	399mm	221mm	Perforated	Anthracite Grey
14825-297	88.1mm	1	399mm	310mm	Perforated	Anthracite Grey
14825-175	43.7mm	1	310mm	221mm	Perforated	Anthracite Grey
14825-375	132.6mm	1	310mm	221mm	Perforated	Anthracite Grey
14825-395	132.6mm	1	399mm	221mm	Perforated	Anthracite Grey
14825-155	43.7mm	1	221mm	221mm	Perforated	Anthracite Grey
14825-397	132.6mm	1	399mm	310mm	Perforated	Anthracite Grey

Table 2/2

Katalogové číslo	Povrchová úprava
14825-154	Aluminum-Zinc Plated, Strukturovaný Práškový
14825-254	Aluminum-Zinc Plated, Strukturovaný Práškový
14825-255	Aluminum-Zinc Plated, Strukturovaný Práškový
14825-197	Aluminum-Zinc Plated, Strukturovaný Práškový
14825-275	Aluminum-Zinc Plated, Strukturovaný Práškový
14825-195	Aluminum-Zinc Plated, Strukturovaný Práškový
14825-295	Aluminum-Zinc Plated, Strukturovaný Práškový
14825-297	Aluminum-Zinc Plated, Strukturovaný Práškový
14825-175	Aluminum-Zinc Plated, Strukturovaný Práškový
14825-375	Aluminum-Zinc Plated, Strukturovaný Práškový
14825-395	Aluminum-Zinc Plated, Strukturovaný Práškový
14825-155	Aluminum-Zinc Plated, Strukturovaný Práškový
14825-397	Aluminum-Zinc Plated, Strukturovaný Práškový

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE