


# Socket Strip, Swiss

Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with Swiss outlets.



## CERTIFICATIONS



## VLASTNOSTI

Socket strips can be rotated through all four directions (in 90° increments) during installation

230 V, 10 A

In accordance with SEV.IEC 60884

Connecting cable 2 m with Swiss version plug

Socket strips Swiss version

Installation height 1 U

Horizontal or vertical mounting

## SPECIFIKACE

|                      |                   |
|----------------------|-------------------|
| <b>Length:</b>       | 438.5mm           |
| <b>Materiál:</b>     | Hliník; Polyamide |
| <b>Barva:</b>        | Grey              |
| <b>Product Type:</b> | Socket Strip      |

Table 1/2

| Katalogové číslo | Typ zásuvky | Socket Quantity | Switched Outlets | Napětí střídavé | Množství v balení | Hloubka |
|------------------|-------------|-----------------|------------------|-----------------|-------------------|---------|
|------------------|-------------|-----------------|------------------|-----------------|-------------------|---------|

|           |       |    |     |      |   |      |
|-----------|-------|----|-----|------|---|------|
| 60110-453 | Swiss | 10 | No  | 230V | 1 | 44mm |
| 60110-454 | Swiss | 9  | Yes | 230V | 1 | 44mm |

Table 2/2

| Katalogové číslo | Povrchová úprava |
|------------------|------------------|
| 60110-453        | Anodized         |
| 60110-454        | Anodized         |

## DALŠÍ PODROBNOSTI O PRODUKTU

Please order bracket for vertical mounting separately.

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Naše portfolio silných značek:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**