

# CompacPRO Filler Angle



The cover bracket is recommended to cover the die cast frame on the left and right side if horizontal rails will be assembled. Provides a better visual look.

## CERTIFICATIONS



## VLASTNOSTI

Cover bracket is recommended in event of expansion with horizontal rails

To cover the sides of the rack and to create a continuous front plane with plug-in units and partial front panels

## SPECIFIKACE

|                          |              |
|--------------------------|--------------|
| <b>Materiál:</b>         | Hliník       |
| <b>Povrchová úprava:</b> | Anodized     |
| <b>Works With:</b>       | Cases        |
| <b>Produktová řada:</b>  | CompacPRO    |
| <b>Product Type:</b>     | Cover        |
| <b>Typ:</b>              | Filler Angle |

Table 1/1

| Katalogové číslo | Rack Height | Množství v balení |
|------------------|-------------|-------------------|
| 24575-019        | 2U          | 2                 |
| 24575-419        | 6U          | 2                 |
| 24575-219        | 4U          | 2                 |
| 24575-119        | 3U          | 2                 |

## DALŠÍ PODROBNOSTI O PRODUKTU

---

Fixing material is supplied with case.

## UPOZORNĚNÍ

---

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Naše portfolio silných značek:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**