

# 19" Assembly Kit M6

## Data Solutions



For standard grounding use a grounding nut and washer on at least one attachment point.

When 19" assembly kit is used with conductive 19" panel mount, grounding cage nuts are not needed.

### CERTIFICERINGER



### FUNKTIONER

Assembly kits for assembly of 19" components into a cabinet

For mounting of front panels, distribution fields or other components on the frame, slide mounts or depth members with square cut-outs

### SPECIFIKATIONER

**Product Type:** Assembly Kit

**Finish:** Forzinket Stål

Table 1/2

| Katalognummer | Length | Pakke mængde | Thread Size | Materiale | Produktfamilie | Type |
|---------------|--------|--------------|-------------|-----------|----------------|------|
|---------------|--------|--------------|-------------|-----------|----------------|------|

|           |      |     |    |           |                                                                                                                                                         |                            |
|-----------|------|-----|----|-----------|---------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------|
| 21190-095 |      | 4   | M6 | Stål, ABS | RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>Comptec, Inpac,<br>MultipacPRO,<br>Varistar CP,<br>Eurorack,<br>Outdoor              | Mounting Kit               |
| 21120-213 |      | 4   | M6 | Stål      |                                                                                                                                                         | Mounting Kit               |
| 21120-196 | 16mm | 4   | M6 | Stål      |                                                                                                                                                         | Mounting Kit,<br>Grounding |
| 21100-435 |      | 8   | M6 | Stål, ABS | RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>Comptec, Inpac,<br>MultipacPRO,<br>Varistar CP,<br>Novastar,<br>Eurorack,<br>Outdoor | Mounting Kit               |
| 21120-199 | 13mm | 100 | M6 | Stål      |                                                                                                                                                         | Mounting Kit,<br>Grounding |
| 21120-198 | 16mm | 50  | M6 | Stål      |                                                                                                                                                         | Mounting Kit,<br>Grounding |
| 21120-197 | 16mm | 32  | M6 | Stål      |                                                                                                                                                         | Mounting Kit,<br>Grounding |
| 21190-435 |      | 32  | M6 | Stål, ABS | RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>Comptec, Inpac,<br>MultipacPRO,<br>Varistar CP,<br>Eurorack,<br>Outdoor              | Mounting Kit               |

|           |  |     |    |           |                                                                                                                           |              |
|-----------|--|-----|----|-----------|---------------------------------------------------------------------------------------------------------------------------|--------------|
| 21101-810 |  | 100 | M6 | Stål, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor | Mounting Kit |
| 21101-809 |  | 50  | M6 | Stål, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor | Mounting Kit |
| 21120-215 |  | 32  | M6 | Stål      |                                                                                                                           | Mounting Kit |
| 21120-214 |  | 50  | M6 | Stål      |                                                                                                                           | Mounting Kit |
| 21120-216 |  | 100 | M6 | Stål      |                                                                                                                           | Mounting Kit |

Table 2/2

| Katalognummer | Works With                                                          | Certificeringer |
|---------------|---------------------------------------------------------------------|-----------------|
| 21190-095     | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS            |
| 21120-213     | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                 |
| 21120-196     | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                 |
| 21100-435     | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS            |
| 21120-199     | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                 |
| 21120-198     | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                 |
| 21120-197     | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                 |
| 21190-435     | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS            |
| 21101-810     | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS            |

| Katalognummer | Works With                                                          | Certificeringer |
|---------------|---------------------------------------------------------------------|-----------------|
| 21101-809     | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS            |
| 21120-215     | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                 |
| 21120-214     | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                 |
| 21120-216     | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                 |

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**